



Locking Devices, Elastomeric, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust Tight Housing

By Bryant
Catalog # BRY28W08



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Yellow
Item Type	30A Watertight Plug
Number Of Poles	3-Pole
Performance	Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
	Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
	UV resistance:All exposed materials are UV stabilized
	Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Plugs
UPC	781786378698

Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

Certifications And Compliance

Industry Standard(s)	IP69K
	Listed to UL498
	Certified to CSA C22.2 No. 42
	Meets NEMA® WD-1, WD-6, and ANSI Standards
	IP66 Suitability
	NSF Certified (plugs, connectors and receptacles)
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY I-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Watertight Wiring Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY28W08-SPEC-EN | REV 6/2024