



# Locking Devices, Elastomeric, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY28W47BK](#)

Watertight Devices, Locking Devices, Elastomeric, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black, Water/Dust-Tight Housing

## Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

## Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

## General

Catalog Number	BRY28W47BK
Color	Black
Item Type	30A Watertight Plug
Number Of Poles	2-Pole
Type	Plugs
UPC	781786378728

## Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in

## Electrical Ratings

Amperage Rating	30 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP69K</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>• IP66 Suitability</li><li>• NSF Certified (plugs, connectors and receptacles)</li></ul>
Nema Rating	L5-30P

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY I-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - BRY28W47BK](#)

