



# Locking Devices, Elastomeric, Female Connector Body, 30A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-Nema, Screw Terminals, Water/Dust-Tight Housing



By Bryant  
Catalog # [BRY29W09](#)

Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 30A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminals, Yellow, Water/Dust-Tight Housing

## Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

## General

Color	Yellow
Item Type	30A Watertight Connector
Number Of Poles	4-Pole
Performance	Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12 UV resistance:All exposed materials are UV stabilized Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Connector Body
UPC	781786378889

## Dimensions

Dimensions	2.77 in x 2.77 in x 5.67 in
Height	5.67 in
Length	2.77 in
Width	2.77 in

## Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

## Certifications And Compliance

Industry Standard(s)	IP69K Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA® WD-1, WD-6, and ANSI Standards IP66 Suitability NSF Certified (plugs, connectors and receptacles)
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY I-7](#) [Catalog Page Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY29W09-SPEC-EN | REV 6/2024