



Locking Devices, Elastomeric, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY29W47](#)



Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

General

Color	Yellow
Item Type	30A Watertight Connector
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none">• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12• UV resistance:All exposed materials are UV stabilized• Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Connector Body
UPC	781786378896

Dimensions

Dimensions	2.77 in x 2.77 in x 5.67 in
Height	5.67 in
Length	2.77 in
Width	2.77 in

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
Nema Rating	L5-30R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY28W47 - Locking Devices, Elastomeric, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY50W54 - Watertight Series Replacement Caps, 30A, Yellow](#)
[BRYWTCS3 - Watertight Replacement Cone Seal, Size 3](#)
[BRYWTB3 - Watertight Replacement Bushing Set, Size 3](#)
[BRY28W47BK - Locking Devices, Elastomeric, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY29W47-SPEC-EN | REV 7/2023