



# Locking Devices, Elastomeric, Female Connector Body Interior, 30A 3-Phase Delta 480V AC, 3- Pole 4-Wire Grounding, L16- 30R, Screw Terminal

By Bryant  
Catalog # [BRY29W76IN](#)



Watertight Devices, Locking Devices, Elastomeric, Receptacle Interior, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16- 30R, Screw Terminal

## General

Item Type	30A 480V Watertight Receptacle Replacement Interior
Number Of Poles	3-Pole
Type	Interiors
UPC	781786378971

## Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

## Conductor Related

Number Of Wires	4-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	L16-30R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY69W76 - Watertight Series, Locking Receptacle, 30A 3-Phase 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-30R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY29W76IN-SPEC-EN | REV 7/2023