



Oh No!
IMAGE COMING SOON

**IEC Pin and Sleeve, Splash Proof
Angled Receptacle, 32 A, 220-240
VAC**

By Bryant
Catalog # [BRY332AR6S](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Female,
Receptacle, 32 A 220-240 VAC, 2-POLE 3-WIRE, Blue, Splash
Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	BRY332AR6S
Color	Blue
Environmental Conditions	IP44
Ingress Protection	IP44
Insulation	Insulated Body
Material	PBT
Mounting Type	Screw Mount
Number Of Poles	2-POLE
Series	Splash Proof
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Type	Angled Receptacle
UPC	781786785212

Electrical Ratings

Amperage Rating	32 A
Current / Amperage Rating	32 A
Dielectric Strength	Withstand 3000V AC
Voltage - Maximum	600 VAC
Voltage Rating	220-240 VAC
Voltage Rating Description	220-240 VAC

Conductor Related

Number Of Wires	3-WIRE
Wire Size	#10 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	VDE, CE
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Sales Drawings - M14042](#)
[Specifications - BRYANT_BRY332AR6S_spec](#)



A Hubbell brand