



IEC Pin and Sleeve, Watertight Receptacle, 32 A, 380-480 VAC

By Bryant
Catalog # [BRY432R3W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Female, Receptacle, 32 A 380-480 VAC, 3-POLE 4-WIRE, Red, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	BRY432R3W
Color	Red
Environmental Conditions	IP67
Ingress Protection	IP67
Insulation	Insulated Body
Material	PBT
Mounting Type	Screw Mount
Number Of Poles	3-POLE
Series	Watertight IP67
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Receptacle
UPC	781786782679



Electrical Ratings

Amperage Rating	32 A
Current / Amperage Rating	32 A
Dielectric Strength	Withstand 3000V AC
Voltage - Maximum	600 VAC
Voltage Rating	380-480 VAC
Voltage Rating Description	380-480 VAC

Conductor Related

Number Of Wires	4-WIRE
Wire Size	#10 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	VDE, CE
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY K-4 Catalog Page](#)
- [Catalog Page - BRY K-5 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Sales Drawings - M14034](#)
- [Specifications - BRYANT_BRY432R3W_spec](#)



A Hubbell brand