



# Cord and Cable Reels, Industrial Cord Reel, With 20A GFCI Module, 45' 12/3, Yellow

By Bryant  
Catalog # BRY45123GF20



Cord and Cable Reels, Industrial Cord Reel, With 20A GFCI Module, 45' 12/3, Yellow

## Application

Bench, Ceiling and Wall Mounted

## General

Base Type	Optional
Cable Length	45 Ft.
Cable Type	#12/3 SJEO
Catalog Number	BRY45123GF20
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	No
Item Type	Reel with 20A 125V AC, GFCI
OEM Brand Name	Hubbell Bryant
Series	Industrial
Type	Reel With Portable Outlet Box And 1-20A 125V GFCI Receptacle
UPC	781786128187

## Dimensions

Cable Length Active	540
Cable Length Inactive	60
Reel Frame Dimension	Steel

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Specification	12/3 SJEO
Feeder Cord	12/3 SJEO
Nema Color	Yellow and Black

## Product Assets

[Literature - General Literature - Electric Cord and Cable Reels Specifications - BRY45123GF20](#)