



IEC Pin and Sleeve, Watertight Plug, 60/63 A, 3 Phase 200-250 VAC

By Bryant
Catalog # [BRY460P9W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Male, Plug, 60/63 A 125/250 VAC, 3-POLE 4-WIRE, Blue, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection

Application

High Ampacity Connections

General

Catalog Number	BRY460P9W
Color	Blue
Environmental Conditions	IP67
Ingress Protection	IP67
Insulation	Insulated Body
Material	PBT
Mounting Type	Cord Mounted
Number Of Poles	3-POLE
Series	Watertight IP67
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plug
UPC	781786782334

Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Dielectric Strength	Withstand 3000V AC
Phase	Three Phase
Voltage - Maximum	600 VAC
Voltage Rating	3 Phase 200- 250 V
Voltage Rating Description	3 Phase 200-250 VAC

Conductor Related

Number Of Wires	4-WIRE
Wire Size	#6 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	All constructions are UL Listed & cUL Listed, FileE14633, UL1686 Standard for Pin & Sleeve Configurations, VDE, CE
Nema Rating	Non-NEMA

Logistics

Carton Quantity	5
Pallet Quantity	150

Product Assets

- [Catalog Page - BRY K-11 Catalog Page](#)
- [Catalog Page - BRY K-4 Catalog Page](#)
- [Catalog Page - BRY K-5 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Sales Drawings - M14030](#)
- [Specifications - BRYANT_BRY460P9W_spec](#)



A Hubbell brand