



**Straight Blade Devices,
Receptacles, Duplex, Weather
Resistant, Commercial/Industrial
Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Single Pack**

By Bryant
Catalog # [BRY5262WWR](#)



Straight Blade Devices, Receptacles, Duplex, Weather Resistant,
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, White, Single Pack

Features

- Duplex
- Weather Resistant
- Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	BRY5262WWR
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Weather Resistant
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786670556

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in

Length	3.28 in
Weight	0.25 lb
Width	1.54 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-8](#) [Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5262WWR](#)