



Straight Blade Devices, Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3- Wire Grounding, 5-15P, Single Pack

By Bryant
Catalog # [BRY5266NPCR](#)



Straight Blade Devices, Male Plug, Corrosion Resistant,
Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15P, Yellow ,Single Pack

Application

Extra Heavy Duty Industrial Grade

General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Type	Plug
UPC	781786134041

Dimensions

Dimensions	2.18 in x 1.52 in x 1.38 in
Display Size	Standard Sized
Height	1.38 in
Length	2.18 in
Weight	0.1 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant J-2 Catalog page](#)
[Catalog Page - Bryant A-20 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY5266NPCR-SPEC-EN | REV 7/2023