



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Orange, Single Pack

By Bryant
Catalog # BRY5266NPOR



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Orange, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial Grade

General

Catalog Number	BRY5266NPOR
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Type	Plug
UPC	781786134010

Dimensions

Dimensions	2.18 in x 1.52 in x 1.38 in
Display Size	Standard Sized
Height	1.38 in
Length	2.18 in

Weight	0.1 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-20 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5266NPOR](#)

