



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R and Black

By Bryant
Catalog # [BRY5269NC](#)



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White and Black, Single Pack

Application

Extra Heavy Duty Industrial Grade

General

Color	Black and White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005945

Dimensions

Dimensions	2.95 in x 1.52 in x 1.38 in
Display Size	Standard Sized Product
Height	1.38 in
Length	2.95 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-20 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - TECH-SPEC® Plugs and Connectors](#)
[Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY5269NC-SPEC-EN | REV 7/2023