



# Straight Blade Devices, Receptacles, Combo Duplex, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown, Single Pack

By Bryant  
Catalog # BRY5292



Straight Blade Devices, Receptacles, Combo Duplex, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown, Single Pack

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	BRY5292
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Combination Receptacle
UPC	781786005174

## Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.3 lb
Width	1.54 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	3750

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R, 6-15R
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-11 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY5292-SPEC-EN | REV 6/2024