



# Straight Blade Devices, Receptacles, Duplex, Weather Resistant, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Single Pack

By Bryant  
Catalog # [BRY5362WWR](#)



Straight Blade Devices, Receptacles, Duplex, Weather Resistant, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

## General

|                              |   |
|------------------------------|---|
| Application                  | Extra Heavy Duty Industrial Specification Grade |
| Catalog Number               | BRY5362WWR                                      |
| Color                        | White   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Weather Resistant                               |
| Item Type                    | Traditional Duplex                              |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 2-Pole  |
| OEM Brand Name               | Hubbell Bryant                                  |
| Series                       | Extra Heavy Duty                                |
| Style                        | Finder Groove Face                              |
| Type                         | Duplex Receptacle                               |
| UPC                          | 781786670631                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 3.28 in x 1.54 in x 1.16 in |
| Display Size | Standard Sized Product      |
| Height       | 1.16 in                     |
| Length       | 3.28 in                     |
| Weight       | 0.25 lb                     |
| Width        | 1.54 in                     |

## Electrical Ratings

|                            |                     |
|----------------------------|---------------------|
| Amperage Rating            | 20 A                |
| Connectivity               | Back and Side Wired |
| Current / Amperage Rating  | 20 A                |
| Current Rating             | 20 A                |
| Phase                      | Single Phase        |
| Voltage Rating             | 125 V               |
| Voltage Rating Description | 125 V               |
| Wattage                    | 2500                |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |

## Certifications And Compliance

|             |       |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - BRY A-8 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY5362WWR-SPEC-EN | REV 6/2024