



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, Specialty, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown, Single Pack

By Bryant
Catalog # BRY5382



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, Specialty, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- Specialty
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	BRY5382
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Specialty Receptacle
UPC	781786005341

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Weight 0.35 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - BRY A-8 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5382](#)