



Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 250V, 2-Pole 3- Wire Grounding, 6-20R, Black and White, Single Pack

By Bryant
Catalog # [BRY5469NC](#)



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 250V, 2-Pole 3- Wire Grounding, 6-20R, Black and White, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 250V
- 2-Pole 3- Wire Grounding

Application

Extra Heavy Duty Industrial Grade

General

Catalog Number	BRY5469NC
Color	Black and White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786005969

Dimensions

Dimensions	2.95 in x 1.52 in x 1.38 in
Display Size	Standard Sized Product
Height	1.38 in

Length	2.95 in
Weight	0.25 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	5400

Product Assets

- [Catalog Page - BRY A-20 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Power Disruption Solutions](#)
- [Literature - General Literature - TECH-SPEC® Plugs and Connectors](#)
- [Specifications - BRY5469NC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY5469NC-SPEC-EN | REV 10/2024