



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 20A 125V and 250V, 2-Pole 3-Wire Grounding, 5-20R and 6- 20R

By Bryant
Catalog # BRY5492I



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 125V and 250V, 2-Pole 3-Wire
Grounding, 5-20R and 6- 20R, Ivory, Single Pack

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	BRY5492I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Combination Receptacle
UPC	781786005457

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.25 lb
Width	1.54 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R, 6-20R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-11 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY5492I-SPEC-EN | REV 6/2024