



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 15A 250V, 2-Pole 3-Wire Grounding, 6- 15R, Single Pack, Marine Version

By Bryant  
Catalog # [BRY5662CR](#)



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 15A 250V, 2-Pole 3-Wire  
Grounding, 6-15R, Yellow, Single Pack, Marine Version

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005525

## Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.2 lb
Width	1.54 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	6-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant J-2 Catalog page](#)  
[Catalog Page - Bryant A-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY5662CR-SPEC-EN | REV 7/2023