



Watertight Series, Locking Receptacle, 15A 125VAC, 2-Pole 3-Wire Grounding, NEMA L5-15R, Yellow

By Bryant
Catalog # [BRY65W47](#)



Watertight Series, Locking Receptacle, 15A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-15R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	15A Watertight Single Receptacle
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) • UV resistance: All exposed materials are UV stabilized • Flammability: UL94V0 (boxes, covers, and plates)
Type	Receptacle
UPC	781786379183

Dimensions

Dimensions	4.56 in x 3.10 in x 2.83 in
Height	2.83 in
Length	4.56 in
Width	3.10 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
----------------------	---

Nema Rating	L5-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY60CM84AK - Watertight Series, Adapter Kit, 1" NPT, Yellow](#)
[BRY60CM88 - Weatherproof Boxes, 1-Gang, Blank Plate, FS/FD Style, Yellow](#)
[BRY60CM83AK - Watertight Series, FD Box, 3/4" NPT, Gray](#)
[BRY60CM83WA - Watertight Series, FD Box, 3/4" NPT, White](#)
[BRY60CM55 - Watertight Series, Angled Adapter, 3/4" NPT, Yellow](#)



A proud member of the Hubbell Family.

