



Locking Devices, Watertight Series, Receptacle, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Yellow

By Bryant
Catalog # BRY65W47D



Watertight Series, Locking Receptacle, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	15A Watertight Duplex Receptacle
Number Of Poles	2-Pole
Performance	Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) UV resistance:All exposed materials are UV stabilized Flammability:UL94V0 (boxes, covers, and plates)
Type	Duplex Receptacle
UPC	781786380325

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	IP69K in use Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA® WD-1, WD-6, and ANSI Standards IP66 Suitability NSF Certified (plugs, connectors and receptacles)
Nema Rating	L5-15R

Product Assets

[Catalog Page - BRY I-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY65W47D-SPEC-EN | REV 6/2024