



Watertight Series, Locking Receptacle, 20A 125/250V AC, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Yellow

By Bryant
Catalog # [BRY67W08](#)



Watertight Series, Locking Receptacle, 20A 125/250V AC, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	20A Watertight Single Receptacle
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) • UV resistance: All exposed materials are UV stabilized • Flammability: UL94V0 (boxes, covers, and plates)
Type	Receptacle
UPC	781786379206

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.10 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRY26W08 - Straight Blade Devices, Female Connector Body, Elastomeric Water Tight, Industrial/Commercial Grade, Straight, 20A 125/250V, Non-NEMA](#)
[BRY60CM83WAK - Watertight Series, Adapter Kit, 3/4" NPT, White](#)
[BRY60CM84WAK - Watertight Series, Adapter Kit, 1" NPT, White](#)
[BRY6084AK - Watertight Series, Adapter Kit, 1" NPT, Gray](#)
[BRY60CM88W - Watertight Series, 1-Gang, Blank Plate, White](#)



A proud member of the Hubbell Family.

