



Watertight Series, Locking Receptacle, 20A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Yellow

By Bryant
Catalog # BRY67W09

Watertight Series, Locking Receptacle, 20A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

Performance

- Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V0 (boxes, covers, and plates)

General

Catalog Number	BRY67W09
Color	Yellow
Item Type	20A Watertight Single Receptacle
Number Of Poles	4-Pole
Type	Receptacle
UPC	781786379213

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.1 in

Electrical Ratings



Amperage Rating	20 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K in use• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY I-6 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY67W09](#)