



Watertight Series, Locking Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Yellow

By Bryant
Catalog # BRY67W49



Watertight Series, Locking Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	20A Watertight Single Receptacle
Number Of Poles	2-Pole
Performance	Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) UV resistance:All exposed materials are UV stabilized Flammability:UL94V0 (boxes, covers, and plates)
Type	Receptacle
UPC	781786379251

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.1 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	IP69K in use Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA® WD-1, WD-6, and ANSI Standards IP66 Suitability NSF Certified (plugs, connectors and receptacles)
Nema Rating	L7-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY I-6](#) [Catalog Page Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY67W49-SPEC-EN | REV 6/2024