



# Watertight Series, Locking Receptacle, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Yellow

By Bryant  
Catalog # [BRY67W75](#)



Watertight Series, Locking Receptacle, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Yellow

## Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

## General

Color	Yellow
Item Type	20A Watertight Single Receptacle
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)</li> <li>• UV resistance: All exposed materials are UV stabilized</li> <li>• Flammability: UL94V0 (boxes, covers, and plates)</li> </ul>
Type	Receptacle
UPC	781786379275

## Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.10 in

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K in use</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
----------------------	---

Nema Rating	L15-20R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[BRY60CM88W - Watertight Series, 1-Gang, Blank Plate, White](#)  
[BRYP14FS - Wallplates and Boxes, Box Covers, 1-Gang, Blank Plate, For Portable Outlet Box, Gray](#)  
[BRY26W75 - Locking Devices, Elastomeric, Male Plug, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY26W75BK - Locking Devices, Elastomeric, Male Plug, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black, Water/Dust-Tight Housing](#)  
[BRY6700 - Weather Proof Series, Lift Cover Assembly, 20A Locking Less Receptacle](#)



