



# Watertight Series, Locking Receptacle, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Yellow

By Bryant  
Catalog # BRY69W08



Watertight Series, Locking Receptacle, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Yellow

## Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

## Performance

- Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)
- UV resistance: All exposed materials are UV stabilized
- Flammability: UL94V0 (boxes, covers, and plates)

## General

Catalog Number	BRY69W08
Color	Yellow
Item Type	30A Watertight Single Receptacle
Number Of Poles	3-Pole
Type	Receptacle
UPC	781786379329

## Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.1 in

## Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP69K in use</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>• IP66 Suitability</li><li>• NSF Certified (plugs, connectors and receptacles)</li></ul>
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY I-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - BRY69W08](#)