



Watertight Series, Locking Receptacle, 30A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-30R, Yellow

By Bryant
Catalog # [BRY69W49](#)



Watertight Series, Locking Receptacle, 30A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-30R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	30A Watertight Single Receptacle
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) • UV resistance: All exposed materials are UV stabilized • Flammability: UL94V0 (boxes, covers, and plates)
Type	Receptacle
UPC	781786379350

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.10 in

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
----------------------	---

Nema Rating	L7-30P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRY6800 - Weather Proof Series, Lift Cover Assembly, 30A Locking Less Receptacle](#)
[BRY60CM84A - Watertight Series, FD Box, 1" NPT, Yellow](#)
[BRY60CM83WAK - Watertight Series, Adapter Kit, 3/4" NPT, White](#)
[BRY6083AK - Watertight Series, Adapter Kit, 3/4" NPT, Gray](#)
[BRY60CM83AK - Watertight Series, FD Box, 3/4" NPT, Gray](#)



A proud member of the Hubbell Family.

