



# Watertight Series, Locking Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, NEMA L14-30R, Yellow

By Bryant  
Catalog # [BRY69W74](#)



Watertight Series, Locking Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, NEMA L14-30R, Yellow

## Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

## General

|                 |  |
|-----------------|--|
| Color           | Yellow   |
| Item Type       | 30A Watertight Single Receptacle   |
| Number Of Poles | 3-Pole   |
| Performance     | <ul style="list-style-type: none"> <li>• Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)</li> <li>• UV resistance: All exposed materials are UV stabilized</li> <li>• Flammability: UL94V0 (boxes, covers, and plates)</li> </ul> |
| Type            | Receptacle   |
| UPC             | 781786379367   |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 4.56 in x 3.10 in x 3.45 in |
| Height     | 3.45 in                     |
| Length     | 4.56 in                     |
| Width      | 3.10 in                     |

## Electrical Ratings

|                            |             |
|----------------------------|-------------|
| Amperage Rating            | 30 A        |
| Voltage Rating             | 125/250 VAC |
| Voltage Rating Description | 125/250 VAC |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #18 AWG to #8 AWG |

## Certifications and Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• IP69K in use</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul> |
|----------------------|---|

|             |         |
|-------------|---------|
| Nema Rating | L14-30R |
|-------------|---------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - Bryant I-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[BRY28W74 - Locking Devices, Elastomeric, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY6800 - Weather Proof Series, Lift Cover Assembly, 30A Locking Less Receptacle](#)  
[BRY60CM83WA - Watertight Series, FD Box, 3/4" NPT, White](#)  
[BRY6083AK - Watertight Series, Adapter Kit, 3/4" NPT, Gray](#)  
[BRY60CM84A - Watertight Series, FD Box, 1" NPT, Yellow](#)



A proud member of the Hubbell Family.

