



Watertight Series, Locking Receptacle, 30A 3- Phase 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-30R, Yellow

By Bryant
Catalog # [BRY69W76](#)



Watertight Series, Locking Receptacle, 30A 3-Phase 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-30R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

General

Color	Yellow
Item Type	30A Watertight Single Receptacle
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes) • UV resistance: All exposed materials are UV stabilized • Flammability: UL94V0 (boxes, covers, and plates)
Type	Receptacle
UPC	781786379381

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.10 in

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
----------------------	---

Nema Rating	L16-30R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRY60CM55W - Watertight Series, Angled Adapter, 3/4" NPT, White](#)
[BRY6083 - Watertight Series, Angled Adapter, 3/4" NPT, Gray](#)
[BRY6083AK - Watertight Series, Adapter Kit, 3/4" NPT, Gray](#)
[BRY60CM88W - Watertight Series, 1-Gang, Blank Plate, White](#)
[BRY6055 - Watertight Angled Adapter, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY69W76-SPEC-EN | REV 7/2023