



# Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord

By Bryant  
Catalog # BRY6MPS

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body , 6' Cord



### General

Application	6 Outlet, Heavy Duty Devices
Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet Series	Straight Blade 5-15R Economy Power Strips (no SPD)
Type	Metallic
UPC	781786141599

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Cord Length	6 ft
-------------	------

### Logistics

Carton Quantity	20
-----------------	----

### Product Assets

- [Catalog Page - BRY D-5 Catalog Page](#)
- [Catalog Page - BRY B-11 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Surge Protection Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY6MPS-SPEC-EN | REV 6/2024