



Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord

By Bryant
Catalog # [BRY6MPS](#)

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body , 6' Cord



Application

6 Outlet, Heavy Duty Devices

General

Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet Series	Straight Blade 5-15R Economy Power Strips (no SPD)
Type	Metallic
UPC	781786141599

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalog Page - Bryant D-5 Catalog page](#)
- [Catalog Page - Bryant B-11 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Surge Protection Devices](#)

Related Products

- [BRY6MPS1050 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 1050 Joules, 6' Cord](#)
- [BRY7PS1050M - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 7\) Receptacles, Metallic Body, 1050 Joules, 6' Cord, Modem Protection](#)
- [BRY8PS2100D - Bryant Wiring Devices, Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.](#)
- [BRY6PS35015 - Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord](#)
- [BRY6PPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Non-Metallic Body, 6' Cord](#)



A proud member of the Hubbell Family.