



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 1050 Joules, 6' Cord

By Bryant
Catalog # [BRY6MPS1050](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6)
Receptacles, Metallic Body, 1050 Joules, 6' Cord

Application

Standard Devices

General

Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
Series	Economy Surge Strips
Type	Metallic
UPC	781786141582

Dimensions

Display Size 1050 Joules

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 20

Product Assets

[Catalog Page - Bryant D-5 Catalog page](#)
[Catalog Page - Bryant B-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[BRY6PS350 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 350 Joules, 6' Cord](#)
[T1254SI6A - Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord](#)
[BRY6PS35015 - Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord](#)
[BRY6MPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Metallic Body, 6' Cord](#)
[BRY6PPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Non-Metallic Body, 6' Cord](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY6MPS1050-SPEC-EN | REV 7/2023