



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 350 Joules, 6' Cord

By Bryant
Catalog # [BRY6PS350](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6)
Receptacles, Metallic Body, 350 Joules, 6' Cord

Application

Standard Devices

General

EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Bryant
Operating Temperature	33 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
UPC	781786141612

Dimensions

Display Size	350 Joules
--------------	------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Catalog Page - Bryant D-5 Catalog page](#)
[Catalog Page - Bryant B-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[BRY6PPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Non-Metallic Body, 6' Cord](#)
[BRY6PS35015 - Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord](#)
[BRY6MPS1050 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 1050 Joules, 6' Cord](#)
[BRY6MPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Metallic Body, 6' Cord](#)
[T1254SI6A - Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord](#)



A proud member of the Hubbell Family.