



Straight Blade Devices, Receptacles, Weather Resistant Duplex, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Gray, Single Pack

By Bryant
Catalog # [BRY8200GRYWR](#)



Straight Blade Devices, Receptacles, Weather Resistant
Duplex, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-
15R, Gray, Single Pack

Application

Hospital Grade

General

| | |
|------------------------------|--------------------|
| Color | Gray |
| Environmental Conditions | Weather Resistant |
| Item Type | Traditional Duplex |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Hospital Grade |
| Style | Finder Groove Face |
| Type | Duplex Receptacle |
| UPC | 781786670150 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.54 in x 1.16 in |
| Display Size | Standard Sized Product |
| Height | 1.16 in |
| Length | 3.28 in |
| Weight | 0.25 lb |
| Width | 1.54 in |

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications and Compliance

| | |
|-------------|-------|
| Nema Rating | 5-15R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant A-3 Catalog page](#)
[Catalog Page - Bryant B-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY8200GRYWR-SPEC-EN | REV 7/2023