



**Straight Blade Devices,
Receptacles, Tamper- Resistant
Duplex, Hospital Grade, 20A 125V,
2-Pole 3-Wire Grounding, 5- 20R,
Ivory, Single Pack**

By Bryant
Catalog # BRY8300ITR

Straight Blade Devices, Receptacles, Tamper- Resistant Duplex,
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R,
Ivory, Single Pack



General

Application	Hospital Grade
Catalog Number	BRY8300ITR
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hospital Grade
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005815

Dimensions

Dimensions	3.28 in x 1.65 in x 2.75 in
Display Size	Standard Sized Product
Height	2.75 in
Length	3.28 in
Weight	0.3 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	4000

Product Assets

- [Catalog Page - BRY A-3 Catalog Page](#)
- [Catalog Page - BRY B-2 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-BRY8300ITR-SPEC-EN | REV 6/2024