



**Straight Blade Devices,  
Receptacles, Tamper- Resistant  
Duplex, Hospital Grade, 20A 125V,  
2-Pole 3-Wire Grounding, 5- 20R,  
Red, Single Pack**

By Bryant  
Catalog # BRY8300RTR



Straight Blade Devices, Receptacles, Tamper- Resistant Duplex,  
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Red,  
Single Pack

**General**

Application	Hospital Grade
Catalog Number	BRY8300RTR
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hospital Grade
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005839

**Dimensions**

Dimensions	3.28 in x 1.65 in x 2.75 in
Display Size	Standard Sized Product
Height	2.75 in
Length	3.28 in
Weight	0.35 lb
Width	1.65 in

**Electrical Ratings**

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

**Certifications And Compliance**

Nema Rating	5-20R
-------------	-------

**Logistics**

Carton Quantity	10
Pallet Quantity	4000

**Product Assets**

- [Catalog Page - BRY A-3 Catalog Page](#)
- [Catalog Page - BRY B-2 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY8300RTR-SPEC-EN | REV 6/2024