



Bryant Wiring Devices, Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.



By Bryant
Catalog # BRY8PS2100D

Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.

General

Application	Standard Devices
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Bryant
Operating Temperature	36 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
UPC	781786141643

Dimensions

Display Size	2100 Joules
--------------	-------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalog Page - BRY D-5 Catalog Page](#)
- [Catalog Page - BRY B-11 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Surge Protection Devices](#)



A Hubbell brand