



# Bryant Wiring Devices, Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.

By Bryant  
Catalog # [BRY8PS2100D](#)



Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.

## Application

Standard Devices

## General

EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Bryant
Operating Temperature	36 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
UPC	781786141643

## Dimensions

Display Size	2100 Joules
--------------	-------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

- [Catalog Page - Bryant D-5 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Surge Protection Devices](#)

## Related Products

- [BRY6PS35015 - Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord](#)
- [BRY6MPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Metallic Body, 6' Cord](#)
- [BRY7PS1050M - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 7\) Receptacles, Metallic Body, 1050 Joules, 6' Cord, Modem Protection](#)
- [T1254SI6A - Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord](#)
- [BRY6MPS1050 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 1050 Joules, 6' Cord](#)



A proud member of the Hubbell Family.