



# Cord and Cable Reels, Commercial Cord Reel, 40' 15A 125V with Triple Tap, Yellow

By Bryant  
Catalog # [BRYC40123TT](#)

Cord and Cable Reels, Commercial Cord Reel, 40' 15A 125V  
with Triple Tap, Yellow



## Application

Bench, Ceiling and Wall Mounted

## General

Base Type	Optional
Cable Length	40 Ft.
Cable Type	#16/3 SJT
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	No
Item Type	Reel with Triple Tap
OEM Brand Name	Hubbell Bryant
Series	Commercial
Type	Reel With Triple Tap 15A 125V Connector
UPC	781786128217

## Dimensions

Cable Length Active	480
Cable Length Inactive	24
Reel Frame Dimension	Steel

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Specification	12/3 SJTW
Feeder Cord	12/3 SJTW
Nema Color	Black

## Product Assets

[Catalog Page - Bryant M-3 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - General Literature - Electric Cord and Cable Reels](#)  
[Literature - Pulp & Paper Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRYC40123TT-SPEC-EN | REV 7/2023