



# Temporary Lighting Products, 34.5", 25W, 2125 Lumen Output, Fluorescent String Light, With Hanging Straps

By Bryant  
Catalog # [BRYFS2549](#)

Temporary Lighting Products, 34.5" , 25W, 2125 Lumen Output,  
Fluorescent String Light, With Hanging Straps



## General

Light Source	Fluorescent
Series	Stringer Lights
Type	Fluorescent Light
UPC	781786380073

## Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

## Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRYFS2549-SPEC-EN | REV 7/2023