BRYANT®

Temporary Lighting Products, 34.5", 25W, 2125 Lumen Output, Fluorescent String Light, With Hanging Straps

By Bryant
Catalog # BRYFS5035

Temporary Lighting Products, 34.5", 25W, 2125 Lumen Output, Fluorescent String Light, With Hanging Straps

General

Light Source	Fluorescent
Series	Stringer Lights
Type	Fluorescent Light
UPC	781786380066

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Product Assets

Literature - General Literature - Temporary Lighting Solutions

©2023 Hubbell Incorporated. All rights reserved.