



Temporary Lighting Products, 28W Light String, With In-Line Switch, 2928 Lumen Output

By Bryant
Catalog # [BRYLS2834](#)

Temporary Lighting Products, 28W Light String, With In-Line Switch, 2928 Lumen Output



General

Light Source	LED
Series	Stringer Lights
Type	LED
UPC	781786380134

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYLS2834-SPEC-EN | REV 7/2023