



Temporary Lighting Products, 6-12', 2000W, 220, 000 Lumen Output Metal Halide Cart Light

By Bryant
Catalog # [BRYMH2000](#)

Temporary Lighting Products, 6-12', 2000W, 220,000 Lumen Output Metal Halide Cart Light



General

Light Source	Metal Halide
Series	Cart Light
Type	Metal Halide
UPC	781786379930

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Wattage	2000 W

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYMH2000-SPEC-EN | REV 7/2023