



# Temporary Lighting Products, 400W High Bay Light, 29, 000 Lumen Output

By Bryant  
Catalog # [BRYMH400](#)

Temporary Lighting Products, 400W High Bay Light, 29,000  
Lumen Output



## General

Light Source	Metal Halide
Series	High Bay Light
Type	Metal Halide
UPC	781786379947

## Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Wattage	400 W

## Product Assets

[Catalog Page - Bryant L-11 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRYMH400-SPEC-EN | REV 7/2023