



Temporary Lighting Products, 48.5" Fluorescent Light, 25W, 2125 Lumen Output, 25' Cord

By Bryant
Catalog # [BRYML2525](#)

Temporary Lighting Products, 48.5" Fluorescent Light, 25W,
2125 Lumen Output, 25' Cord



General

Light Output	2125 lm
Light Source	Fluorescent
Series	Portable work Light
Type	Fluorescent Maintenance Light
UPC	781786379855

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Wattage	25 W

Conductor Related

Cord Length	25 ft
-------------	-------

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYML2525-SPEC-EN | REV 7/2023