



## Temporary Lighting Products, LED Maintenance Light, 28W, 2928 Lumen Output, 25' Cord

By Bryant  
Catalog # [BRYML2825L](#)

Temporary Lighting Products, LED Maintenance Light, 28W, 2928 Lumen Output, 25' Cord



### General

Light Output	2928 lm
Light Source	Fluorescent
Series	Portable work Light
Type	LED
UPC	781786379862

### Electrical Ratings

Wattage	28 W
---------	------

### Conductor Related

Cord Length	25 ft
-------------	-------

### Product Assets

[Catalog Page - Bryant L-13 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRYML2825L-SPEC-EN | REV 7/2023