



Temporary Power Products, Spider II Portable Power, Work Lights, Worklight and Cord, 15A 125V, Yellow, Straight Blade, 25'

By Bryant
Catalog # BRYTW25F1



Temporary Power Products, Spider II Portable Power, Work Lights, Worklight and Cord, 15A 125V, Yellow, Straight Blade, 25'

General

| | |
|--------------|-----------------------|
| Light Output | 825 lm |
| Light Source | Fluorescent |
| Series | Portable work Light |
| Type | Fluorescent Worklight |
| UPC | 781786380141 |

Electrical Ratings

| | |
|---------------------------|---------|
| Current / Amperage Rating | 15 A |
| Voltage Rating | 125 VAC |
| Wattage | 13 W |

Conductor Related

| | |
|-------------|-------|
| Cord Length | 25 ft |
|-------------|-------|

Product Assets

- [Catalog Page - BRY L-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Temporary Lighting Solutions](#)