



Temporary Power Products, Spider II PortablePower, Work Lights, Worklight and Cord, 15A 125V, Yellow, Locking, 25'

By Bryant
Catalog # [BRYTW25F2](#)



Temporary Power Products, Spider II PortablePower, Work Lights, Worklight and Cord, 15A 125V, Yellow, Locking, 25'

General

Light Output	825 lm
Light Source	Fluorescent
Series	Portable work Light
Type	Fluorescent Worklight
UPC	781786380158

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Wattage	13 W

Conductor Related

Cord Length	25 ft
-------------	-------

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)