



Temporary Lighting Products, LED Work Light with End Light and Tool Tap, 25', 16/3 SJTOW Cord

By Bryant
Catalog # BRYWL25LEDT

Temporary Lighting Products, LED Work Light with End Light and Tool Tap, 25', 16/3 SJTOW Cord



General

Light Output	920 lm
Light Source	LED
Series	Portable work Light
Type	LED
UPC	781786379886

Electrical Ratings

Wattage	9 W
---------	-----

Conductor Related

Cord Length	25 ft
-------------	-------

Product Assets

- [Catalog Page - BRY L-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Temporary Lighting Solutions](#)