



Temporary Lighting Products, Fluorescent Light, Class 1 Div 1, 12V, 26W, 1800 Lumen Output

By Bryant
Catalog # [BRYXF50120V](#)



Temporary Lighting Products, Fluorescent Light, Class 1 Div 1,
12V, 26W, 1800 Lumen Output

General

Environmental Conditions	Hazardous Location
Light Output	1800 lm
Light Source	Fluorescent
Series	Portable work Light
Type	Fluorescent Light
UPC	781786379794

Electrical Ratings

Wattage	26 W
---------	------

Conductor Related

Cord Length	50 ft
-------------	-------

Certifications and Compliance

Certification	<ul style="list-style-type: none">• Class 1, Div 1 Groups C & D• Class 2, Div 1 Groups F & G
---------------	---

Product Assets

[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRYXF50120V-SPEC-EN | REV 7/2023